

Seitz® AKS FB Sheets

For Color and Flavor Correction

Seitz AKS FB series depth filter sheets were developed to satisfy general purpose carbon adsorption applications in the food and beverage industry.

Description

Powdered activated carbon (PAC) is widely used in the food and beverage industry for adsorption applications. The use of bulk PAC has significant drawbacks relating to the handling of bulk carbon powder, cleaning of the process equipment, as well as time and costs associated with carbon removal from the process.

Seitz AKS immobilized carbon filter media alleviates these concerns by incorporating activated carbon within a matrix of cellulosic fibers. This immobilized carbon media can be coupled with a downstream protective filter paper to prevent any possible carbon particle shedding downstream of the filter. Additionally, the adsorption efficiency of Seitz AKS immobilized carbon filter media is greater than an equivalent amount of bulk powdered activated carbon (PAC), reducing overall process time and increasing product yield. An internal comparative study using the same carbon grade showed up to 150% better color removal efficiency when compared to bulk PAC.

Features

Carbon-impregnated media with a homogeneous and consistent matrix

High adsorption efficiency as compared to PAC

General-duty media targeted to food and beverage industry needs

Benefits


- Free of carbon dust
- Simplified handling and cleaning
- When using protection paper downstream, no further trap filtration required

- Reduction of overall process time
- Increased product yield
- Good permeability with excellent filtrate quality

- High economic efficiency due to a long service life

Quality

- Manufactured according to ISO 9001:2015 certified Quality Management System



Seitz AKS FB Sheets

Food Contact Compliance

Please refer to the Pall website www.pall.com/foodandbev for a Declaration of Compliance to specific National Legislation and/or Regional Regulatory requirements for food contact use.

Main Constituents

Cellulose, powdered activated carbon

Applications

- Correction of off color, flavor and odors in distilled spirits
- Color removal in cannabis
- Color removal in hard seltzer
- Decolorization of sweetener and sugar syrups
- Color correction in juice and beer applications
- Dechlorination of water
- Gelatin decolorization and deodorization

Adsorption Capability

At an optimized flow rate, the probability of contact between the impurities and carbon particles is greater in carbon impregnated sheets. This is due to process fluids more efficiently contacting carbon particles immobilized into a sheet matrix. Because of the depth (thickness) of the sheet, it is possible to consider the structure as being made up of a series of layers containing PAC. Having a depth of PAC and passing the fluid at an optimal flow rate through that depth enables maximum utilization of the carbon.

Macro- and mesopores can generally be regarded as the highways into the carbon particle, and are crucial for adsorption kinetics. Macropores are used for the transport, and adsorption occurs in the meso- and micropores.

Small molecules, such as methylene blue, which has a molecular weight of 319.86 Dalton, are mainly captured in micropores. Typically, over 200 g/m² methylene blue is adsorbed.

Characterization

Sheet with Protection Paper	Mass per Unit Area g/m ²	Thickness mm	Ash %	Water Permeability ¹ L/m ² /min (gal/f/min)
No	1250	4.5	<1	352 (8.63)
Yes	1250	4.5	<1	189 (4.60)

These figures have been determined in accordance with in-house test methods and the methods of the Technical / Analytical Work Group within the European Depth Filtration Association.

¹ The permeability was measured under test conditions with clean water at 20 °C (68 °F) and a Δp of 1 bar (14.5 psi).

Regeneration

Depending upon the application and the nature of the adsorbed contaminants, AKS series filter sheets may be regenerated by means of rinsing with clean water in the forward direction. However, the achievable regeneration efficiency must be determined by monitoring filtrate quality.

Sterilization and Sanitization

Method	Temperature °C (°F)	Maximum Differential Pressure bar (psi)	Time ² /Cycle min
Steam	125 (257)	0.5 (7.2)	20
Hot Water	90 (194)	1 (14.5)	30

² The actual time required may vary as a function of the process conditions.

General Instructions for Use

To achieve optimal filtrate quality, Pall recommends the use of protection paper downstream. Sheet options which include a downstream protection paper are available³.

In order to maximize the required adsorption of impurities, particle filtration must occur upstream of carbon-impregnated filter sheets.

Filtration Guidelines

Typical flux rates used on food and beverage fluids are 150-250 L/m²/h (3.7-6.2 gal/ft²/h).

Higher fluxes may be possible according to the application. Due to the various factors, which may affect the adsorption process, Pall recommends an initial scaled-down testing as a reliable method of qualifying filter performance.

For additional operating guidelines, including rinsing of sheets prior to use, please refer to instructions for use or contact Pall.

Available Sheet Formats³

Rectangular Sheets

400 mm x 400 mm (15.8" x 15.8")

600 mm x 612 mm (23.6" x 24.1")

³ Sheets are available with or without downstream protection paper. Please indicate which type is required upon order placement.

Other formats are available on request.

Seitz AKS FB series filter sheets are also available in SUPRADisc™ I module configuration. Please contact Pall.



+1-866-905-7255 **Food and Beverage toll free**
foodandbeverage@pall.com

Corporate Headquarters
Port Washington, NY, USA
+1-800-717-7255 toll free (USA)
+1-516-484-5400 phone

European Headquarters
Fribourg, Switzerland
+41 (0)26 350 53 00 phone

Asia-Pacific Headquarters
Singapore
+65 6389 6500 phone

Visit us on the Web at www.pall.com/foodandbev

Pall Corporation has offices and plants throughout the world. To locate the Pall office or distributor nearest you, visit www.pall.com/contact.

The information provided in this literature was reviewed for accuracy at the time of publication. Product data may be subject to change without notice. For current information consult your local Pall distributor or contact Pall directly.

IF APPLICABLE Please contact Pall Corporation to verify that the product conforms to your national legislation and/or regional regulatory requirements for water and food contact use.

© Copyright 2023, Pall Corporation. Pall, , Seitz and SUPRADisc are trademarks of Pall Corporation. ® Indicates a trademark registered in the USA.

FBDSAKSFBENC
JUNE 2023