

PC110 Designed for the A320 Family

Improve the cabin environment, reduce delays and enhance safety

The Pall A-CAF (Advanced Cabin Air Filter) offers exceptional cabin air quality by ensuring dust, fibres, allergens, viruses, Volatile Organic Compounds (VOCs) and odours are removed from the recirculation air stream.

Recirculation of cabin air was introduced in the 1960s and 1970s as a measure to reduce fuel costs. To ensure that the air being recirculated inside the cabin was free of bacteria and viruses, Pall introduced High-Efficiency Particulate Arrestance (or HEPA) filters. Continuously seeking to improve filtration performance to meet the needs of the industry and traveling public alike, Pall is now introducing A-CAF (Advanced Cabin Air Filter).



A-CAF (Advanced Cabin Air Filtration) is the combination of HEPA with an advanced activated carbon that further enhances aircraft cabin air quality by removing contaminants and odours, increasing crew and passenger comfort and improving airline operational efficiency.

FEATURES / BENEFITS

- Unique immobilised activated carbon matrix
- Removes VOCs that may be present in the cabin, including degraded engine oil products, de-icing fluids or hydraulic fluids from the re-circulated air
- Eliminates unpleasant odours within the cabin
- Reduces number of unscheduled diversions (related to contaminated air events)
- Reduces unnecessary maintenance activities associated with non-persistent/transitional odour events
- Enhances overall cabin air quality and ensures crew and passenger comfort

PERFORMANCE




Figure 1 illustrates the effectiveness of the A-CAF in reducing odours and VOCs from a cabin.

With its installation, a fume event or odour present in the cabin will be reduced to non-detectable levels within 3 minutes after the onset (Time 0).

Without an odour filter in place, the event can take over 10 minutes to dissipate to an acceptable level.

	HEPA ONLY FILTER P/N: QA06423-01	HEPA/VOC FILTER P/Ns: QB0654-01 / QB0654-02
PARTICULATE REMOVAL	99.99% NaCl removal efficiency to EN1822-1 H14	
MICROBIAL REMOVAL	>99.999% removal when challenged with Brevundimonas diminuta, Bascillus subtilis and MS2 Coliphage virus	
VOC REMOVAL	Not designed to remove gases	High adsorption efficiency for a wide variety of gaseous contaminants/odors (chemical dependent)
WEIGHT	3.0 KG (spec weight 4.8 KG)	4.7 KG
ESTIMATED CHANGE INTERVAL	5,000 HRS or 36 months in AIRBUS MPD	5,000 HRS or 36 months (recommended)
DIMENSIONS	OD 345 by 500mm length	OD 345 by 500mm length
INTERCHANGEABILITY	The two filters are inter-changeable	
APPROVALS	OEM Production Standard	QB0654-01: Pall DOA no. EASA 21J.477 QB0654-02: FAA PMA PQ1063CE


ORDERING INFORMATION

Pall P/Ns: QB0654-01 / QB0654-02

For the airline aftermarket, these filters are available through our authorised airline distributor, Satair A/S, www.satair.com. Satair/also provides global 24/7 technical support service to our airline customers. Technical data presented in this product data sheet represents only a fraction of the test program that has taken place to demonstrate the effectiveness of this advanced filter. For further details, facts and figures, please get in touch:

pureair@pall.com





PALL Pall Corporation

Pall Aerospace

US: New Port Richey, FL telephone: +1 727-849-9999 toll free US: +1 800-933-3111

UK: Portsmouth telephone: +44 (0)23 9233 8000 email: aerospace@pall.com

VISIT aerospace.pall.com

Because of technological developments related to the products, systems, and/or services described herein, the data and procedures are subject to change without notice. Please consult your Pall representative or visit www.pall.com to verify that this information remains valid.

© Copyright 2019, Pall Corporation. Pall and (are trademarks of Pall Corporation. ® indicates a trademark registered in the USA.

BETTER LIVES. BETTER PLANET. and **Filtration. Separation. Solution.SM** are service marks of Pall Corporation.