

# FMO High Flow Series Filter Housings

## High Flow 316L Stainless Steel Multi-Cartridge Filter Housing for Industrial Applications

- Accepts 12 or 21, 30<sup>"</sup> (76.2 cm) or 40<sup>"</sup> (102 cm) Filter Cartridges
- Housing is Designed to Accept DOE, M3 (Code 3) or M8 (Code 8) Style Filter Cartridges
- 316L Stainless Steel Material of Construction for Corrosion Resistance
- Swing Bolt Closure Design Assures Secure Sealing and Ease of Change Outs
- Side-In/Side-Out Design Allows for Easy Piping
- 150 PSIG (10.3 BAR) Maximum Operating Pressure Permits Use in Many Applications
- 1" (2.5 cm) Drain Ports Allow Rapid Evacuation of Vessel

# **Housing Specifications**

## Maximum Operating Pressure:

150 psig (10.3 bar) @ 200°F (93°C)

NOTE: Maximum operating pressure ratings are vessel ratings only. Safe operating temperature and pressure will depend on filter cartridge and gasket/O-ring used. For inquiries on compatibility, contact the factory or your Pall distributor.

#### Construction:

Head:	316L Stainless steel
Shell:	316L Stainless steel
Connections:	316L Stainless steel
Bolting:	Zinc Plated Steel

#### Connections:

NSI RF Flange
NSI RF Flange
NPT
IPT

Shell O-rings:	EPDM (standard), Buna N,
	Silicone Elastomer, Viton <sup>1</sup> A

#### **Customization:**

Housings can be engineered to meet the specific needs of the process and installation. Contact your Pall distributor or Technical Services for assistance.


<sup>1</sup> Registered trademark of DuPont Dow.



## **Dimensional Data (nominal)**

Model	# Columns	<b>Dimensions</b> (inches)						Flow Rate <sup>2</sup> (gpm)	Weight In Ibs. (Empty)
		Α	В	C	D	E	F		
36FM03	12	56 (142.2 cm)	12 (30.5 cm)	31 (78.7 cm)	19 (48.3 cm)	12 (30.5 cm)	16 ¾ (41.6 cm)	180 (681 lpm)	220 (100 kg)
48FM04	12	66 (167.6 cm)	12 (30.5 cm)	31 (78.7 cm)	19 (48.3 cm)	12 (30.5 cm)	16 ¾ (41.6 cm)	240 (909 lpm)	235 (107 kg)
63FM03	21	57 (144.8 cm)	16 (40.6 cm)	31 (78.7 cm)	19 (48.3 cm)	12 (30.5 cm)	20 ¾ (52.7 cm)	315 (1192 lpm)	285 (129 kg)
84FM04	21	67 (170.2 cm)	16 (40.6 cm)	31 (78.7 cm)	19 (48.3 cm)	12 (30.5 cm)	20 <sup>3</sup> ⁄ <sub>4</sub> (52.7 cm)	420 (1590 lpm)	305 (138 kg)

<sup>2</sup> For viscosity and specific gravity similar to water.



# **Part Numbers/Ordering Information**

■ FMO ● – 316L – ◆F – 💿 (e.g., 63FMO3-316L-4F-IP)

Code	No. of 10" Equivalents	Code		Cartridge Lengths	
36	36	1	3	30″	
48	48		4	40″	
63	63	•			
84	84	-			

Code	Inlet/Outlet Connection Sizes	
3	3" for 36 and 48	
4	4" for 63 and 84	

Code ©	Internal Parts <sup>3</sup>			
Blank	No Internal Parts			
IP	Internal Parts			

3 Standard vessels include internal parts of top seat plates and tube guides. Basic vessels without internal parts may be ordered as non-stock items.



# Pall Corporation

2200 Northern Boulevard East Hills, New York 11548-1289

1.800.FILTERS toll free 516.484.5400 phone 516.484.0364 fax information@pall.com e-mail

# Visit us on the Web at www.pall.com

Pall Corporation has offices and plants throughout the world in locations including: Argentina, Australia, Austria, Belgium, Brazil, Canada, China, France, Germany, Hong Kong, India, Indonesia, Ireland, Italy, Japan, Korea, Malaysia, Mexico, the Netherlands, New Zealand, Norway, Poland, Puerto Rico, Russia, Singapore, South Africa, Spain, Sweden, Switzerland, Taiwan, Thailand, United Kingdom, United States, and Venezuela. Distributors are located in all major industrial areas of the world.

Filtration. Separation. Solution.sm

© Copyright 2004, Pall Corporation. Pall and (ALL) are trademarks of Pall Corporation. © Indicates a Pall trademark registered in the USA. *Filtration. Separation. Solution.su* is a service mark of Pall Corporation.