



r e g e n e r a b l e

PMM® Filter Elements


Description

PMM® medium is a thin, sintered matrix of 316L stainless steel powder within the pore structure of stainless steel wire mesh. It combines the best qualities of Pall PSS® sintered powder medium and Pall Rigimesh® sintered woven wire mesh medium. The **PMM** filter is designed so that the sintered bonds are at the points of contact, producing an extremely strong porous material whose wires do not shift and whose pore size integrity is continuously maintained. Designs are available suitable for temperatures up to 1250°F (677°C).

Operating Characteristics

Standard cartridges are capable of withstanding a minimum collapse differential pressure of 125 psid (8.6 bard) in the forward flow (outside-in) direction at up to 600°F† (315°C) and 10 psid (.7 bard) in the reverse flow direction. Optional design available for 50 psid (3.4 bard) reverse flow.

† Threaded connector series only. Due to seal limitations, 1000 Series suitable for applications up to 450°F (232°C).



Sizes

The standard **PMM** filters are cylindrical forms, 2-1/2" in diameter in 10" multiple lengths, up to 40". For AB style **PMM** filters consult the factory.

Technical Information

Table 1. PMM elements and their characteristics

Filter Grade	Removal Ratings						Clean Pressure Drop				Recommended Flow Density	
	Liquid Service ⁽¹⁾				Gaseous Service ⁽²⁾		Liquid Service		Gaseous Service		Aqueous gpm/ft ²	Air acfm/ft ²
	Rating at % Efficiency (µm)				Weight % Removal	100% Removal (µm)	Aqueous ⁽³⁾ psi/gpm/ft ² mbar/lpm/m ³	Air ⁽⁴⁾ psi/acfm/ft ² mbar/m ³ /hr/m ²				
90%	99%	99.9%	100%									
M020	0.1	0.5	1	2	>99.99	0.4	0.87	1.47	0.093	.350	0.1-75	3-10
M050	0.6	2	4	5	99.99	0.6	0.49	.83	0.051	.192	0.1-75	3-10
M100	2	5	8	10	99.97	1.3	0.28	.47	0.030	.113	0.2-1	5-20
M150	5	9	12	15	99.96	2.5	0.17	.29	0.017	.064	0.5-3	7-25
M200	8	13	16	20	99.93	4.0	0.07	.12	0.007	.026	0.7-4	10-30
M250	10	16	21	25	99.90	9.0	0.02	.03	0.002	.008	1-5	15-40

- (1) Liquid removal efficiency ratings are based on a modified F2 test method and actual particle count data.
 (2) Weight percent removal data is based on AC Fine Test Dust in air. Absolute retention ratings based on actual particle count.

- (3) Pressure drop obtained by multiplying value shown by actual flow desired, viscosity of liquid in centipoise (if other than 1 cp), all divided by total filtration area selected. See Table II for areas.
 (4) Pressure drop in obtained by multiplying value shown by actual gaseous flow rate desired, ratio of viscosities, all divided by total filtration area selected. See Table II for areas.

Part Numbers/Ordering Information

Table II. Standard Configurations of PMM Elements

100% Removal Rating (µm)	PMM Series Element Part Numbers	
	1000 Series	Threaded Element 1000 Series
2	MBS 100 ■ M020 ▲	P24 ◆● M020 ▼
5	MBS 100 ■ M050 ▲	P24 ◆● M050 ▼
10	MBS 100 ■ M100 ▲	P24 ◆● M100 ▼
15	MBS 100 ■ M150 ▲	P24 ◆● M150 ▼
20	MBS 100 ■ M200 ▲	P24 ◆● M200 ▼
25	MBS 100 ■ M250 ▲	P24 ◆● M250 ▼

Code	Code	Nominal Length (in.)	Area ft ² m ²
1	10	10	1.5 .14
2	20	20	3.0 .28
3	30	30	4.5 .42
4	40	40	6.0 .26

Code	Gasket Option
H13 (Std.)	Buna N (Nitrile)
H	Viton*
J	Ethylene Propylene
J7	Ethylene Propylene for Steam Service
RE	Reinforced for 50 psid (3.4 bard) reverse flow

Code	Connection
4	1" NPT
6	1 1/2" NPT

Code	Other Options
RE	Reinforced for 50 psid (3.4 bard) reverse flow
C9	Cleaned for oxygen service

*Trademark of E.I. du Pont de Nemours & Co.

Housing Information

A full selection of standard Pall industrial housings are available for **PMM** elements. Threaded connector elements are designed to fit a special line of housings capable of a broader range of temperature (cryogenic to 800°F) (426°C) and chemical service. Custom designed housings for specific applications are also available.



New York - USA

888 873 7255 toll free in the USA
 +1 516 484 5400 phone
 +1 516 484 0364 fax
 fuelsandchemicals@pall.com email

Portsmouth - Europe

+44 (0)23 9230 3303 phone
 +44 (0)23 9230 2506 fax
 fuelsandchemicals@pall.com email

Visit us on the Web at www.pall.com

Because of developments in technology these data or procedures may be subject to change. Consequently we advise users to review their continuing validity annually.

Pall Corporation has offices and plants throughout the world in locations including: Argentina, Australia, Austria, Belgium, Brazil, Canada, China, France, Germany, Hong Kong, India, Indonesia, Ireland, Italy, Japan, Korea, Malaysia, Mexico, the Netherlands, New Zealand, Norway, Poland, Puerto Rico, Russia, Singapore, Spain, South Africa, Sweden, Switzerland, Taiwan, Thailand, United Kingdom, the United States and Venezuela. Distributors are located in all major industrial areas of the world.

© Copyright 2001, Pall Corporation. Pall, and Centrasette are trademarks of Pall Corporation.
 * Indicates a Pall trademark registered in the USA. Filtration. Separation. Solution.sm is a service mark of Pall Corporation. Pure-Flo is a registered trademark of ITT Industries, Inc.