

New: Retrofit for Peco GoldXtream™ Filter Element



PFTM5740V266/PFTM_740V266

Introducing Pall's filter technology for users of Peco GoldXtream™ filters in:

- Gas Processing (Amine and glycol regeneration loops)
- Gas Production (Produced water)
- Hydrocarbon Refining (Liquid feedstocks; product polishing; amine regeneration; water wash)
- Water and Wastewater (Raw water feeds; Wastewater disposal and release)

Pall's new retrofit filters allow users of Peco GoldXtream™ elements to benefit from Pall expertise without the need to replace the existing housing/vessel. Pall retrofit filters are direct replacements for existing GoldXtream™ elements offering the performance and value you have come to expect from Pall.

Advantages of Pall Technology

Pall's filter media and element designs bring together industry leading technologies and advanced manufacturing processes to deliver unsurpassed performance and value in each and every element.

Pall Retrofit features

- Pleated media for high filtration surface
- High void volume for high dirt-holding capacity
- Broad range of chemical compatibility for maximum application utility

Specifications

- Maximum Operating Differential Pressure: 3.4 bard (50 psid) @ 79°C (175°F)
- Materials of construction
 - Polypropylene media, support and endcaps
 - Tin coated steel center core

Global Presence – Local Support

Pall is a global company with offices in Asia, Americas, Europe, and the Middle East. This global presence gives us the ability to provide local commercial or technical support whenever or wherever there is a customer need. Contact us if you have specific GoldXtream™ configuration not listed in this datasheet.

Competitor P/N	Brand	Rating	Media	O-Ring	Pall-Fit P/N
PHD-639 01LV	GoldXtream™ filter	1µm	PP depth	Fluorocarbon	RPF003UY639S0010V
PHD-639 03LV	GoldXtream™ filter	3µm	PP depth	Fluorocarbon	RPF003UY639S0030V
PHD-639 05LE	GoldXtream™ filter	5µm	PP depth	EPR	PFTM1740E
PHD-639 05LV	GoldXtream™ filter	5µm	PP depth	Fluorocarbon	PFTM5740V266
PHD-639 10LV	GoldXtream™ filter	10µm	PP depth	Fluorocarbon	PFTM10740V
PHD-639 20LB	GoldXtream™ filter	20µm	PP depth	Buna	PFTM20740N266



PALL CORPORATION

Corporate Headquarters

Port Washington, NY, USA
+1-800-717-7255 toll free (USA)
+1-516-484-5400 phone

European Headquarters

Fribourg, Switzerland
+41 (0)26 350 53 00 phone

Asia-Pacific Headquarters

Singapore
+65 6389 6500 phone

Visit us on the Web at www.pall.com/industry

Contact us at www.pall.com/contact

Pall Corporation has offices and plants throughout the world. To locate the Pall office or distributor nearest you, visit www.pall.com/contact.

The information provided in this literature was reviewed for accuracy at the time of publication. Product data may be subject to change without notice. For current information consult your local Pall distributor or contact Pall directly.

IF APPLICABLE Please contact Pall Corporation to verify that the product conforms to your national legislation and/or regional regulatory requirements for water and food contact use.

© Copyright 2021, Pall Corporation. Pall, are trademarks of Pall Corporation.

® Indicates a trademark registered in the USA.
GoldXtream is a trademark of Peco.