

Small Flow Emflon® Filter



Description

The Small Flow Emflon filter is recommended for chemicals which are compatible with PTFE and polypropylene.

- High flow rates
- Wide variety of configurations
- Three removal ratings available
- Integrity testable
- Low extractables
- Optimized design
- Manufactured in a cleanroom environment
- 100% integrity tested

Specifications

Materials

- Medium: PTFE
- Core, cage, and end caps: Polypropylene
- Support and drainage: Polypropylene
- O-ring options: Viton,¹ Teflon¹ encapsulated Viton, and ethylene propylene

Removal Ratings

- 1 µm, 0.2 µm, 0.1 µm

Filter Areas

- 2.3 ft² / .22 m² per 2230 cartridge
- 4.7 ft² / .44 m² per 4463 cartridge
- 3.8 ft² / .35 m² per 4440 cartridge

Configurations


- Nominal length: 2.5" / 64 mm and 5" / 127 mm
- Diameter: 2.25" / 57 mm
- O-ring size / end caps:
 - 2230 (116 internal O-ring / flat end)
 - 4463 (116 internal O-ring / flat end)
 - 4440 (118 double O-ring / flat end)

Operating Conditions


- Maximum Temperature: 194°F / 90°C
- Maximum Forward Differential Pressure:
 - 80 psid @ 120°F / 5.5 bar @ 50°C;
 - 50 psid @ 121° - 195°F / 3.5 bar @ 51° - 90°C

¹ Viton and Teflon are trademarks of DuPont Dow Elastomers


Pressure Drop vs. Liquid Flow Rate²



Cartridge Style 2230



Cartridge Style 4440



Cartridge Style 4463

² For liquids with viscosity differing from water, multiply the pressure drop by the viscosity in centipoise.

Part Numbers / Ordering Information

Part Number	Removal Rating (μm)	Nominal Length (in / mm)	O-Ring Size / Material ³
MDY2230FNEHF	1.0	2.5 / 64	116 / Viton A
MCY4463FNEHF	1.0	5.0 / 127	116 / Viton A
MDY2230FREHF	0.2	2.5 / 64	116 / Viton A
MCY4463FREHF	0.2	5.0 / 127	116 / Viton A
MCY4440FREHF ⁴	0.2	5.0 / 127	118 / Viton A
MDY2230FTEJ	0.1	2.5 / 64	116 / Ethylene Propylene
MCY4463FTEHF	0.1	5.0 / 127	116 / Viton A

³ Other O-ring materials are available.

⁴ Designed to retrofit competitor's 40 stack cartridges.

Unit conversion: 1 bar = 100 kilopascals



2200 Northern Boulevard
East Hills, New York 11548-1289 USA

1.800.360.7255 toll free (Only in US)
1.516.484.5400 phone
1.516.625.3610 fax

Filtration. Separation. Solution.SM

Visit us on the Web at www.pall.com/micro

Pall Corporation has offices and plants throughout the world in locations including: Argentina, Australia, Austria, Belgium, Brazil, Canada, China, France, Germany, Hong Kong, India, Indonesia, Ireland, Italy, Japan, Korea, Malaysia, Mexico, the Netherlands, New Zealand, Norway, Poland, Puerto Rico, Russia, Singapore, South Africa, Spain, Sweden, Switzerland, Taiwan, Thailand, United Kingdom, United States, and Venezuela. Distributors are located in all major industrial areas of the world.

© Copyright 2004, Pall Corporation. Pall, are trademarks of Pall Corporation. ® Indicates a Pall trademark registered in the USA. Filtration. Separation. Solution.SM is a service mark of Pall Corporation.