

Megaplast™ G2 Filter Housing

Description

The Megaplast G2 housing is designed to accommodate 102 mm / 4 in., 254 mm / 10 in. and 508 mm / 20 in. filter cartridges up to 82.5 mm / 3.25 in. in diameter. The connections are molded directly into the head and bowl, reducing the space required for fit up. These housings are designed to meet the stringent cleanliness requirements of ultrapure applications by utilizing PFA for all wetted components.

- High-purity design
- Metal-free construction
- High temperature capability
- Closure threads are on the "dry" side
- · Closure nut is free floating
- Cleaned and packaged under controlled cleanroom conditions

Specifications

Materials1

- Molded high-purity PFA head with molded connections
- Molded high-purity PFA bowl with molded vent and drain
- Closure nut: PTFE or PVDF
- Mounting bolts: PVDF (glass-filled)
- O-ring²: FEP encapsulated fluoroelastomer

Configurations

- Connection Options:
 3/4 in., 1 in. male flare style
 3/4 in. NPT
 3/4 in., 1 in. Butt weld
- 102 mm / 4 in., 254 mm / 10 in., and 508 mm / 20 in. cartridges (double 222 O-ring / flat end) up to 82.5 mm / 3.25 in. diameter
- Vent / drain connections
 1/4 in., 1/2 in. male flare style
 1/4 in. NPT
 1/4 in., 1/2 in. Butt weld
- Mounting bolts: 4 hex bolts M8 x 80 + nut




Operating Conditions

Maximum Operating Pressure:
 5.6 bar @ 30°C / 80 psig @ 86°F
 3.8 bar @ 60°C / 55 psig @ 140°F
 2.8 bar @ 95°C / 40 psig @ 200°F

¹ PFOA free fluoropolymer


² Other o-ring options available

Pressure Drop vs. Liquid Flow Rate³



 $^{^{\}rm 3}$ For liquids other than water, multiply the pressure drop by the specific gravity of the fluid.

Dimensions



Ordering Information

Part Number ⁴	Description	Inlet/Outlet	Vent Drain	Length (L) (mm/in.)
PFGF04F13H1	102 mm / 4 in. Housing PVDF Collar Nut	¾ in. flare style	1/4 in. flare style	247 / 9.72
PFGF04F17H1	102 mm / 4 in. Housing PVDF Collar Nut	1 in. flare style	½ in. flare style	251 / 9.88
PFGF04N12H1	102 mm / 4 in. Housing PVDF Collar Nut	¾ in. NPT	1/4 in. NPT	227 / 8.94
PFGF04P12H1	102 mm / 4 in. Housing PVDF Collar Nut	¾ in. Butt Weld	1/4 in. Butt Weld	242 / 9.53
PFGF04P16H1	102 mm / 4 in. Housing PVDF Collar Nut	1 in. Butt Weld	½ in. Butt Weld	242 / 9.53
PFGF1F13H1	254 mm / 10 in. Housing PVDF Collar Nut	¾ in. flare style	1/4 in. flare style	377 / 14.85
PFGF1F17H1	254 mm / 10 in. Housing PVDF Collar Nut	1 in. flare style	½ in. flare style	381 / 15.0
PFGF1N12H1	254 mm / 10 in. Housing PVDF Collar Nut	¾ in. NPT	1/4 in. NPT	357 / 14.06
PFGF1P12H1	254 mm / 10 in. Housing PVDF Collar Nut	¾ in. Butt Weld	1/4 in. Butt Weld	372 / 14.65
PFGF1P16H1	254 mm / 10 in. Housing PVDF Collar Nut	1 in. Butt Weld	½ in. Butt Weld	372 / 14.65
PFGF2F13H1	508 mm / 20 in. Housing PVDF Collar Nut	¾ in. flare style	1/4 in. flare style	639 / 25.16
PFGF2F17H1	508 mm / 20 in. Housing PVDF Collar Nut	1 in. flare style	½ in. flare style	643 / 25.31
PFGF2N12H1	508 mm / 20 in. Housing PVDF Collar Nut	¾ in. NPT	½ in. NPT	619 / 24.37
PFGF2P12H1	508 mm / 20 in. Housing PVDF Collar Nut	3/4 in. Butt Weld	1/4 in. Butt Weld	634 / 24.96
PFGF2P16H1	508 mm / 20 in. Housing PVDF Collar Nut	1 in. Butt Weld	½ in. Butt Weld	634 / 24.96

Spanner Wrench part number: ACS0655AA

⁴ For liquids other than water, multiply the pressure drop by the specific gravity of the fluid. Unit conversion: 1 bar = 100 kilopascals





25 Harbor Park Drive
Port Washington, NY 11050
+1 516 484 3600 telephone
+1 800 360 7255 toll free US





Pall Corporation has offices and plants throughout the world in locations including: Argentina, Australia, Australia, Belgium, Brazil, Canada, China, France, Germany, Hong Kong, India, Indonesia, Ireland, Italy, Japan, Korea, Malaysia, Mexico, the Netherlands, New Zealand, Norway, Poland, Puerto Rico, Russia, Singapore, South Africa, Spain, Sweden, Switzerland, Taiwan, Thailand, United Kingdom, United States, and Venezuela. Distributors are located in all major industrial areas of the world

[©] Copyright 2014, Pall Corporation. Pall, ALL), and Megaplast are trademarks of Pall Corporation. ® indicates a trademark registered in the USA. BETTER LIVES. BETTER PLANET. and Filtration. Separation. Solution.sм are service marks of Pall Corporation.