

Profile® III Filter (50 nm) for Advanced CMP Applications

Description

The Profile® III 50 nm Filter has been developed to classify CMP slurries used in today's most advanced technologies. Pall's latest advancements in its melt-blowing processes have been utilized to produce extremely fine fibers that make it possible to remove large particles in slurries with mean particle size as low 30 nm, while being able to maintain an extremely low pressure drop across the filter.

These technology advancements make the Profile III, the filter of choice for next generation ceria and silica slurries.

Features & Benefits

- Multi-zone pore construction optimizes both retention and filter service life
- Each zone is manufactured to a target specification ensuring consistent, reproducible performance




Materials of Construction

Components	Materials
Filter media	Polypropylene
Core, Cage, End caps	Polypropylene
O-ring	Ethylene Propylene (EPR)

Specifications

Configurations	Code 25	Code 7
Nominal Length	AB04 : 118 mm / 4.6 in AB1 : 276 mm / 10.9 in AB2 : 524 mm / 20.6 in AB3 : 777 mm / 30.6 in AB4 : 1,032 mm / 40.6 in	AB04 : 165 mm / 6.5 in AB1 : 320 mm / 12.6 in AB2 : 569 mm / 22.4 in AB3 : 817 mm / 32.2 in AB4 : 1,066 mm / 42.0 in
Nominal Diameter	70 mm / 2.75 in	
Removal Ratings	50 nm	
Maximum Operating Temperature	82 °C / 180 °F	
Maximum Forward Differential Pressure	0.41 MPa @ 30 °C / 60 psid @ 85 °F 0.34 MPa @ 50 °C / 50 psid @ 122 °F 0.2 MPa @ 70 °C / 30 psid @ 158 °F 0.1 MPa @ 82 °C / 15 psid @ 180 °F	

Typical Flow Characteristics – 1 cP fluid, 20 °C



Part Numbers / Ordering Information

AB 1 W0005 2 J

Table 1

Code	Cartridge Nominal Length
04	4"
1	10"
2	20"
3	30"
4	40"

Table 2

Code	O-ring Size / End Caps
25	222 double O-ring flat end
7	226 double O-ring bomb fin



Pall Corporation

Microelectronics

25 Harbor Park Drive
Port Washington, NY 11050
+1 800 360 7255 toll free US
+1 516 484 3600 telephone
+1 516 801 9711 fax

Nihon Pall Ltd.

6-5-1, Nishishinjuku,
Shinjuku-ku
Tokyo 163-1325 Japan
+81 3 6901 5700 telephone
+81 3 5322 2109 fax

Visit us on the Web at microelectronics.pall.com

Pall Corporation has offices and plants throughout the world. For Pall representatives in your area, please go to www.pall.com/corporate_contact.asp.

Because of technological developments related to the products, systems, and/or services described herein, the data and procedures are subject to change without notice. Please consult your Pall representative or visit www.pall.com to verify that this information remains valid.

© Copyright 2019, Pall Corporation. Pall, , and Profile are trademark of Pall Corporation.

® Indicates a Pall trademark registered in the USA. **Filtration. Separation. Solution.SM** is a service mark of Pall Corporation.